

Technical data sheet

1015 D fastening clip

Item number: 1009461



Fastening clip with a central fastening point for 2 cables or 2 pipes



St	Steel
G	Electrogalvanized

Master data

Item number	1009461
Type	1015 D 8 G
Description 1	Fastening clip
Description 2	for 2 cables
Manufacturer	OBO
Dimension	8mm
Material	Steel
Surface	Electrogalvanized
Surface standard	EN ISO 19598 / EN ISO 4042
Smallest sales unit	100
Unit of quantity	Piece
Weight	1.15 kg
Weight unit	kg/100 pc.
CO2 Footprint (GWP) Cradle-to-Gate	0,0101 kg COe / 1 Piece


Technical data sheet

1015 D fastening clip

Item number: 1009461



Dimensions



Length	43 mm
Width	12 mm
Height	9 mm
Dimension A	43 mm
Dimension b	12 mm
Dimension H	9 mm

Technical data

Distance to the wall	no
Number of cables/pipes	2
Version for	Single-lobe
Fastening type	Screw hole
For diameter	8
Suitable in fire protection area	no
Halogen-free	yes
Plastic-covered	no
Hole size	6,5 mm
Material thickness	1.5 mm
Nominal diameter	8 mm
Clamping range D, min.	8 mm
UV-resistant	yes