

# Technical data sheet

## Expansion piece, metric thread

Item number: 2088284



Extension made from brass with metric inner and outer thread to mount metal or plastic cable glands on housings. IP54 protection rating without additional connection sleeve. Protection rating of up to IP68 possible with additional connection seal, such as an O-ring or flat sealing ring.



Brass



Nickel-plated

### Master data

Item number	2088284
Type	165 ADA M32-40
Description 1	Extension
Description 2	M - M
Manufacturer	OBO
Dimension	M32-M40
Material	Brass
Surface	Nickel-plated
Surface standard	
Smallest sales unit	25
Unit of quantity	Piece
Weight	5.18 kg
Weight unit	kg/100 pc.
CO Footprint (GWP) Cradle-to-Gate	0,1357 kg COe / 1 Piece

# Technical data sheet


## Expansion piece, metric thread

Item number: 2088284



### Dimensions

Dimension D	26 mm
Dimension E	45.5 mm
Dimension G1 (mm)	32
Dimension G2 (mm)	40
Dimension L	23.8 mm
Dimension L1	8 mm
Dimension L2	10 mm
Dimension L4	5 mm



### Technical data

explosion-proof	no
Thread type: External thread	Metric
Thread type: Internal thread	Metric
Thread dimension, metric, external	32
Thread dimension, metric, internal	40
WAF	42
Nickel-plated	yes