

Technical data sheet

Expansion piece, metric thread

Item number: 2088286



Extension made from brass with metric inner and outer thread to mount metal or plastic cable glands on housings. IP54 protection rating without additional connection sleeve. Protection rating of up to IP68 possible with additional connection seal, such as an O-ring or flat sealing ring.



CuZn
37 Brass

N Nickel-plated

Master data

Item number	2088286
Type	165 ADA M 50-63
Description 1	Extension
Description 2	M - M
Manufacturer	OBO
Dimension	M50-M63
Material	Brass
Surface	Nickel-plated
Surface standard	
Smallest sales unit	5
Unit of quantity	Piece
Weight	13.06 kg
Weight unit	kg/100 pc.
CO Footprint (GWP) Cradle-to-Gate	0,3966 kg COe / 1 Piece

Technical data sheet


Expansion piece, metric thread

Item number: 2088286



Dimensions

Dimension D	43.4 mm
Dimension E	69.9 mm
Dimension G1 (mm)	50
Dimension G2 (mm)	63
Dimension L	33 mm
Dimension L1	9.2 mm
Dimension L2	16 mm
Dimension L4	7 mm



Technical data

explosion-proof	no
Thread type: External thread	Metric
Thread type: Internal thread	Metric
Thread dimension, metric, external	50
Thread dimension, metric, internal	63
WAF	65
Nickel-plated	yes