

Technical data sheet

GTPL hat profile rail, perforated

Item number: 1115669



Hat profile rail 35 x 7.5 mm to DIN EN 60715 (formerly DIN EN 50022).



- St

Steel
- GTP

Electrogalvanized, transparently passivated

Master data	
Item number	1115669
Type	2069 2M GTPL
Description 1	Top hat rail
Description 2	perforated
Manufacturer	OBO
Dimension	2000x35x7,5
Material	Steel
Surface	Electrogalvanized, transparently passivated
Surface standard	
Smallest sales unit	2
Unit of quantity	Metre
Weight	33.28 kg
Weight unit	kg/100 m
CO Footprint (GWP) Cradle-to-Gate	0,6257 kg COe / 1 Meter


Technical data sheet

GTPL hat profile rail, perforated

Item number: 1115669



Dimensions



Length	2,000 mm
Width	35 mm
Height	7.5 mm

Technical data

Version for	Perforated
Version, rails	Support rail DIN EN 60715
Drill hole spacing, centre	25 mm
Bundle	50 m
Hole shape (ETIM)	Long slot
Material thickness	1 mm