

# Technical data sheet

## 90° Quick pipe bend, light grey

Item number: 2153870



Fitting for plastic electrical installation pipes to create 90° bends. Suitable for Quick Pipe pipes or corrugated pipes. Toolless closing and opening. Can be used in a temperature range of -25 to +60 °C.



**PVC** Polyvinylchloride

### Master data

Item number	2153870
Type	2953 B M32 LGR
Description 1	90° Quick pipe bend
Manufacturer	OBO
Dimension	M32
Colour	Light grey; RAL 7035
Material	Polyvinylchloride
Smallest sales unit	5
Unit of quantity	Piece
Weight	3.917 kg
Weight unit	kg/100 pc.

### Dimensions

Dimension B	38.7 mm
Dimension L	102.7 mm
Dimension L1	42 mm
Dimension R	22 mm

# Technical data sheet

90° Quick pipe bend, light grey

Item number: 2153870



## Technical data

Version for	Connector
Flexible	no
For nominal pipe diameter	32 mm
Halogen-free	no
With inspection opening and lid	no
With sleeve	no
Brushed surface	no
Polished surface	no
Permitted temperature range, max.	60 °C
Permitted temperature range, min.	0 °C
Angle of the bend	90 °
Two-part	yes