

Technical data sheet

ISO base clip

Item number: 2130254



ISO base clip 22.5–25 mm



PS

Polystyrene

Master data

Item number	2130254
Description 1	ISO base clip
Manufacturer	OBO
Dimension	22,5-25mm
Colour	Light grey; RAL 7035
Material	Polystyrene
Smallest sales unit	25
Unit of quantity	Piece
Weight	1.221 kg
Weight unit	kg/100 pc.


Technical data sheet

ISO base clip

Item number: 2130254



Dimensions



Dimension A	55 mm
Dimension B	43 mm
Dimension d	23 mm
Dimension H	16 mm
Dimension x	3 mm

Technical data

Number of cables/pipes	1
Version for	Closed
Fastening type	Screw hole
Suitable in fire protection area	no
Thread	M6
Size	Pg 9
Halogen-free	yes
Plastic-covered	no
Bolt	M5 x 14
Clamping range D, max.	25 mm
Clamping range D, min.	22.5 mm
UV-resistant	no