

Technical data sheet

ISO base clip

Item number: 2130408



ISO base clip 36.5–40 mm



PS

Polystyrene

Master data

Item number	2130408
Description 1	ISO base clip
Manufacturer	OBO
Dimension	36,5-40mm
Colour	Light grey; RAL 7035
Material	Polystyrene
Smallest sales unit	20
Unit of quantity	Piece
Weight	3.017 kg
Weight unit	kg/100 pc.


Technical data sheet

ISO base clip

Item number: 2130408



Dimensions



Dimension A	80 mm
Dimension B	66 mm
Dimension d	34 mm
Dimension H	23 mm
Dimension x	4 mm

Technical data

Number of cables/pipes	1
Version for	Closed
Fastening type	Screw hole
Suitable in fire protection area	no
Thread	M6
Size	Pg 9
Halogen-free	yes
Plastic-covered	no
Bolt	M5 x 18
Clamping range D, max.	40 mm
Clamping range D, min.	36.5 mm
UV-resistant	no