

Technical data sheet

Adhesive clip 4040, without nail

Item number: 2215314



Adhesive clip, for clamping to the cable, suitable for steel nails 2 mm.



PP Polypropylene

Master data

Item number	2215314
Type	4040
Description 1	Self-retaining clip
Description 2	no nail
Manufacturer	OBO
Dimension	7-12mm
Colour	Light grey; RAL 7035
Material	Polypropylene
Smallest sales unit	100
Unit of quantity	Piece
Weight	0.053 kg
Weight unit	kg/100 pc.
CO2 Footprint (GWP) Cradle-to-Gate	0,0022 kg CO2e / 1 Piece


Technical data sheet

Adhesive clip 4040, without nail

Item number: 2215314



Dimensions



Dimension B	8.3 mm
Dimension H	10.1 mm
Dimension L	19.1 mm

Technical data

Double clip	no
Shape	Round (for round conductor)
for cable diameter, max.	12 mm
for cable diameter, min.	7 mm
For nail diameter	2
Hardened	no
Halogen-free	yes
With nail	no
Impact-resistant	yes
Pipe locking	no