

Technical data sheet

Fastening clip 822, heavy duty, FT

Item number: 1014501



Fastening clip, single-lobe, 25 mm



- St

Steel
- FT

Hot-dip galvanised

Master data		
Item number	1014501	
Type	822 25 FT	
Description 1	Fastening clip	
Description 2	single lobe	
Manufacturer	OBO	
Dimension	25mm	
Material	Steel	
Surface	Hot-dip galvanised	
Surface standard	DIN EN ISO 1461	
Smallest sales unit	50	
Unit of quantity	Piece	
Weight	2.4 kg	
Weight unit	kg/100 pc.	
CO Footprint (GWP) Cradle-to-Gate	0,0735 kg COe / 1 Piece	


Technical data sheet

Fastening clip 822, heavy duty, FT

Item number: 1014501



Dimensions



Length	53 mm
Width	20 mm
Height	23.5 mm
Dimension A	11 mm
Dimension b	20 mm
Dimension D	25 mm
Dimension H	23.5 mm
Dimension L	25.5 mm
Dimension L1	53 mm
Dimension t	3 mm

Technical data

Distance to the wall	no
Number of cables/pipes	1
Version for	Single-lobe
Fastening type	Screw hole
For diameter	25
Suitable in fire protection area	no
Size	M25
Halogen-free	yes
Plastic-covered	no
Hole size	6,5 x 10 mm
Material thickness	2 mm
Nominal diameter	25 mm
UV-resistant	yes