

# Technical data sheet

## Suspension bracket, black

Item number: 6363875



Suspension bracket for cable support systems to fasten directly under the ceiling or as a suspension with threaded rods M10. Black coated.



Steel



PES135 - Polyester

### Master data

|                     |                     |
|---------------------|---------------------|
| Item number         | 6363875             |
| Type                | AHB 100 FTK SW      |
| Description 1       | Suspension bracket  |
| Description 2       | flat steel          |
| Manufacturer        | OBO                 |
| Dimension           | B100mm              |
| Colour              | Jet black; RAL 9005 |
| Material            | Steel               |
| Surface             | PES135 - Polyester  |
| Surface standard    |                     |
| Smallest sales unit | 1                   |
| Unit of quantity    | Piece               |
| Weight              | 54.4 kg             |
| Weight unit         | kg/100 pc.          |


# Technical data sheet

## Suspension bracket, black

Item number: 6363875



### Dimensions



|             |        |
|-------------|--------|
| Length      | 30 mm  |
| Width       | 127 mm |
| Height      | 180 mm |
| Dimension B | 115 mm |

### Technical data

|                                  |                              |
|----------------------------------|------------------------------|
| Version for                      | Suspension bracket (C clamp) |
| F in kN ceiling                  | 0.6 kN                       |
| Maintain electrical functions    | no                           |
| for width max.                   | 100 mm                       |
| for width min.                   | 100                          |
| Suitable for metric threaded rod | 10                           |
| Suitable for mesh cable tray     | no                           |
| Suitable for cable ladder        | no                           |
| Suitable for cable tray          | yes                          |
| Suitable for tray/ladder width   | 100 mm                       |
| Hole diameter                    | 11 mm                        |
| Material thickness               | 6 mm                         |
| Tray fastening                   | Screw-on                     |
| Adjustable                       | no                           |