Technical data sheet Cable tray BKRS 100 FS

Item number: 6062000



Heavy-duty, walkable cable tray system BKRS with base perforation, in 100 mm side height.

The cable tray has connector perforations on both sides.

Straight connectors should be ordered separately and in the appropriate quantity. Magnetic shield insulation without cover 20 dB, with cover 50 dB.



Master data

Item number	6062000
Description 1	Cable tray BKRS
Description 2	walkable
Manufacturer	OBO
Dimension	100x100x3000
Colour	zinc
Material	Steel
Surface	Strip galvanized
Surface standard	DIN EN 10346
Smallest sales unit	3
Unit of quantity	Metre
Weight	469.8 kg
Weight unit	kg/100 m
CO Footprint (GWP) Cradle-to- Gate	11,3504 kg COe / 1 Meter

Technical data sheet Cable tray BKRS 100 FS

Item number: 6062000



Dimensions		
	Length	3,000 mm
	Length	10 ft
	Width	100 mm
	Width	4 in
	Height	100 mm
	Height	4 in
	Plate thickness	0.08 in
	Plate thickness	2 mm
	Dimension B	100 mm
	Dimension H	100 mm
	Dimension L	3,000 mm

Technical data

Connector version	Without connectors
Mounting system fastening type	Floor
Walkable	yes
Maintain electrical functions	no
With cover	no
Mounting perforation in base	yes
NATO hole pattern	no
Usable cross-section	84 cm ²
Usable cross-section	8352 mm²
Rustproof steel, pickled	no
Side perforation	no
Wide-span version	no
Load test type according to IEC 61537	Туре II
Type of connector, cable support system	Screwed