

Technical data sheet

CM3015 profile rail, slot 16 mm, FS, perforated

Item number: 1110002



Profile rail, perforated, slot width 16 mm.



- St** Steel
- FS** Strip galvanized

Master data	
Item number	1110002
Type	CM3015P2000FS
Description 1	Profile rail
Description 2	perforated, slot 16mm
Manufacturer	OBO
Dimension	2000x30x15
Material	Steel
Surface	Strip galvanized
Surface standard	DIN EN 10346
Smallest sales unit	2
Unit of quantity	Metre
Weight	69 kg
Weight unit	kg/100 m
CO2 Footprint (GWP) Cradle-to-Gate	1,7075 kg COe / 1 Meter


Technical data sheet

CM3015 profile rail, slot 16 mm, FS, perforated

Item number: 1110002



Dimensions



Length	2,000 mm
Width	30 mm
Height	15 mm
Dimension L	2,000 mm

Technical data

Breakable	no
Type of perforation	Perforated back
Version for	Single profile
Drill hole spacing, centre	25 mm
Bundle	20 m
Maintain electrical functions	no
Material thickness	1.5 mm
With perforation	yes
With toothing	no
Profile shape	C profile
Slot width	16 mm
Static value A	0.8 cm ²
Static value Iy	0.24 cm
Static value Iz	1.22 cm
Static value Wy	0.29 cm ²
Static value Wz	0.81 cm ²