

# Technical data sheet

Deskbox DB, freely placeable, 2+2 sockets, 2x RJ45 Cat. 6

Item number: 6116918



Deskbox with connection cable, cable outlet on the left and right housing cover, freely placeable using non-slip support points.

## Equipment:

- Two black protection contact sockets in 0° connection direction, incl. 3.0 m power cable with angular connector CEE 7/7, cable exit on the left housing cover.
  - Two red protection contact sockets in 0° connection direction, incl. 3.0 m power cable with angular connector CEE 7/7, cable exit on the left housing cover.
  - Two data technology couplings RJ45 to RJ45, 1:1 switched, Cat. 6 shielded, cable exit on the right housing cover.
- The ready-for-connection type DB Deskbox is particularly suitable for the direct supply of workstations with energy, communication and data technology connections.




**Alu** Aluminium

## Master data

Item number	6116918
Type	DB-0A3 D22SR2K
Description 1	Desk box
Description 2	free erection
Manufacturer	OBO
Colour	aluminium
Material	Aluminium
Smallest sales unit	1
Unit of quantity	Piece
Weight	100 kg
Weight unit	kg/100 pc.

## Dimensions



Length	300 mm
Width	73 mm
Height	70 mm

# Technical data sheet

Deskbox DB, freely placeable, 2+2 sockets, 2x RJ45 Cat. 6

Item number: 6116918



## Technical data

Number of audio connections	0
Number of CAT 5 connections	0
Number of CAT 5E connections	0
Number of CAT 6 connections	2
Number of USB connections	0
Number of VGA connections	0
Number of HDMI connections	0
Number of SCHUKO sockets	4
Version for	Housing, silver anodised
Version for	Structure
Extendable	no
Shape	Rectangular
Foldable	no
Length of the supply cable	3 m
Surge protection	no