

Technical data sheet

Earthing kit, earth rod standard, 6 m

Item number: 5000756



- 4 x earth rods, type 219 20 ST/FT 1.5 m for depths up to 6 m
- With impact point, hammer head, connection clip, type 2760 20 FT, corrosion protection bandage
- With spigot and drill hole for arrangement
- Corresponds to the requirements of VDE 0185-305 (IEC 62305)
- Short-circuit current I_k (50 Hz), time 1 s, temp. max. 300 °C: 7.9 kA (219 20 ST)



Master data

Item number	5000756
Type	EK 219 20 ST FT
Description 1	Earthing kit standard
Description 2	up to a depth of 6 m
Manufacturer	OBO
Dimension	4x1500
Smallest sales unit	1
Unit of quantity	Piece
Weight	0 kg
Weight unit	kg/100 pc.

Technical data

Version for	Miscellaneous
Design earth rod	Standard
Lightning current carrying capacity	H/100 kA
Profile type	Round D=20 mm
Connection type	With pin/drill hole