


Technical data sheet

Truss-head bolt with nut and washer F

Item number: 6407560



Truss-head bolt with square neck including hexagonal nut and washer.
Quality 8.8



St

Steel


F

Hot galvanized

Master data

Item number	6407560
Type	FRS 10x25 F 8.8
Description 1	Truss-head bolt
Description 2	with washer and nut
Manufacturer	OBO
Dimension	M10x25
Colour	zinc
Material	Steel
Surface	Hot galvanized
Surface standard	DIN 267, Teil 10
Smallest sales unit	50
Unit of quantity	Piece
Weight	4.5 kg
Weight unit	kg/100 pc.
CO Footprint (GWP) Cradle-to-Gate	0,0135 kg COe / 1 Piece

Dimensions



Length	25 mm
Dimension D	24 mm
Dimension d	10 mm
Dimension L	25 mm

Technical data sheet

Truss-head bolt with nut and washer F

Item number: 6407560



Technical data

Resistance grade	8.8
Thread metric	10
With nut	yes
WAF	17