

# Technical data sheet

End piece, for device installation trunking Rapid 80 type  
GA-90210  
Item number: 6279670



End piece for tidy closure of the Rapid 80 GA device installation trunking in aluminium.



**Alu** Aluminium

## Master data

Item number	6279670
Type	GA-E90210RW
Description 1	End piece
Manufacturer	OBO
Dimension	90x210x37
Colour	Pure white; RAL 9010
Material	Aluminium
Smallest sales unit	1
Unit of quantity	Piece
Weight	18.8 kg
Weight unit	kg/100 pc.
CO2 Footprint (GWP) Cradle-to-Gate	2,3757 kg CO2e / 1 Piece

# Technical data sheet


End piece, for device installation trunking Rapid 80 type

GA-90210

Item number: 6279670



## Dimensions



Length	37 mm
Width	210 mm
Height	90 mm

## Technical data

Version for	Symmetrical
Fastening type	Lockable
for duct width	210 mm
for trunking height	90 mm
Suitable for	Left/right
Halogen-free	yes
Cut lamination	no
Protection rating	IP30
Protective film	yes
Protection rating IK code	IK10
Permitted temperature range, max.	60 °C
Permitted temperature range, min.	-25 °C