


Technical data sheet

External corner, symmetrical, for device installation trunking Rapid 80 type GA-S70170

Item number: 6279110



External corner for changing the direction of the Rapid 80 GA aluminium device installation trunking.
The visible surfaces of the fittings are laminated. The cover must be ordered separately.



Alu Aluminium

Master data

Item number	6279110
Type	GA-SA70170RW
Description 1	External corner
Description 2	symmetrical
Manufacturer	OBO
Dimension	70x170x300
Colour	Pure white; RAL 9010
Material	Aluminium
Smallest sales unit	1
Unit of quantity	Piece
Weight	202.2 kg
Weight unit	kg/100 pc.
CO2 Footprint (GWP) Cradle-to-Gate	27,0526 kg CO2e / 1 Piece

Technical data sheet

External corner, symmetrical, for device installation trunking Rapid 80 type GA-S70170


Item number: 6279110



Dimensions



Length	300 mm
Width	170 mm
Height	70 mm



Technical data

Number of covers	1
Version for	Base
for duct width	170 mm
for trunking height	70 mm
Halogen-free	yes
Cable retaining clip	no
Duct connector	no
Cover mounting type	Internal
Mounting perforation in base	no
Cover width	76.5 mm
Protection rating	IP30
Protective film	yes
Protection rating IK code	IK10
Symmetrical	yes
Permitted temperature range, max.	60 °C
Permitted temperature range, min.	-25 °C
Angle range, min.	90 mm