


Technical data sheet

External corner, symmetrical, for device installation trunking Rapid 80 type GA-S90130

Item number: 6276910



External corner for changing the direction of the Rapid 80 GA aluminium device installation trunking.
The visible surfaces of the fittings are laminated. The cover must be ordered separately.



Alu Aluminium

Master data

Item number	6276910
Type	GA-SA90130RW
Description 1	External corner
Description 2	symmetrical
Manufacturer	OBO
Dimension	90x130x300
Colour	Pure white; RAL 9010
Material	Aluminium
Smallest sales unit	1
Unit of quantity	Piece
Weight	199.6 kg
Weight unit	kg/100 pc.
CO2 Footprint (GWP) Cradle-to-Gate	28,4137 kg CO2e / 1 Piece

Technical data sheet

External corner, symmetrical, for device installation trunking Rapid 80 type GA-S90130


Item number: 6276910



Dimensions



Length	300 mm
Width	130 mm
Height	90 mm



Technical data

Number of covers	1
Version for	Base
for duct width	130 mm
for trunking height	90 mm
Halogen-free	yes
Cable retaining clip	no
Duct connector	no
Cover mounting type	Internal
Mounting perforation in base	no
Cover width	76.5 mm
Protection rating	IP30
Protective film	yes
Protection rating IK code	IK10
Symmetrical	yes
Permitted temperature range, max.	60 °C
Permitted temperature range, min.	-25 °C
Angle range, min.	90 mm