

Technical data sheet

GES4 service outlet with locking slider

Item number: 7405146



Service outlet with locking slider for up to 6 individual Modul 45 devices in 2 UT3 universal supports, use in duct systems and system floors for indoor use.

Floor covering recess in the hinged cover pre-adjusted to 5 mm, if necessary adjustable to 3, 8 or 10 mm.
Up to 4 installation devices can be used with 50 mm central plate.

Service outlet with locking slider, 2-compartment, for the installation of MT4 mounting support. Two type APMT2 cover plates can be installed.

Floor covering recess in the hinged cover pre-adjusted to 5 mm, if necessary adjustable to 3, 8 or 10 mm.



PA

Polyamide

Master data

Item number	7405146
Description 1	Service outlet
Description 2	for universal mounting
Manufacturer	OBO
Dimension	222x222x65
Colour	Graphite black; RAL 9011
Material	Polyamide
Smallest sales unit	1
Unit of quantity	Piece
Weight	124 kg
Weight unit	kg/100 pc.
CO Footprint (GWP) Cradle-to-Gate	3,5884 kg COe / 1 Piece


Technical data sheet

GES4 service outlet with locking slider

Item number: 7405146



Dimensions



Length	222 mm
Width	222 mm
Height	65 mm

Technical data

Number of installable devices	6
Number of mounting boxes	2
Version for	Square
Cable outlet version	Swivellable cord outlet
Floor covering protection frame	yes
Floor care	Dry
Seal installation option	no
Screed height, min.	73 mm
Floor height, min.	73 mm
Suitable for raised floor installation	yes
Suitable for screed-flush closed underfloor ducts	no
Suitable for screed-covered underfloor ducts	yes
Suitable for cavity floor installation	yes
Suitable for wet care	no
Suitable for underfloor box	250/350
Suitable for underfloor ducts	yes
Device support to accept mounting boxes	yes
Length of external dimensions	222 mm
Length of installation dimensions	201 mm
With floor covering recess	yes
Nominal size for device installation units	4
Frame version	Carpet protection frame
Protection rating (IP) when used	IP20
Protection rating (IP) when unused	IP40
Protection rating IK code	IK08
Heavy-duty version	no
Installation system type	UT3

Technical data sheet

GES4 service outlet with locking slider

Item number: 7405146



Technical data

Vertical load, large area	to 3,000 N
Vertical load, small area	to 2,000 N
Approvals	VDE
Opening mechanism	Locking slider
Floor covering thickness	5 mm
Bodenbelagdicke max.	10 mm