

Technical data sheet

External corner hood, for device installation trunking Rapid 45-2 type GK-53165
Item number: 6113424



External corner for changing the direction of Rapid 45-2 device installation trunking. The fittings can be adjusted between 80–110°.



Polycarbonate/Acrylnitrile-butadiene-styrene

Master data


Item number	6113424
Type	GK-AH53165AL
Description 1	External corner
Description 2	variable
Manufacturer	OBO
Dimension	175x88x88
Colour	aluminium
Material	Polycarbonate/Acrylnitrile-butadiene-styrene
Smallest sales unit	1
Unit of quantity	Piece
Weight	9.23 kg
Weight unit	kg/100 pc.

Technical data sheet


External corner hood, for device installation trunking Rapid
45-2 type GK-53165
Item number: 6113424



Dimensions



Length	88 mm
Width	175 mm
Height	55 mm



Technical data sheet

External corner hood, for device installation trunking Rapid
45-2 type GK-53165
Item number: 6113424



Technical data

Version for	Hood fitting
for duct width	165 mm
for trunking height	53 mm
Halogen-free	yes
Cable retaining clip	no
Duct connector	no
Cover mounting type	Cross-over
Mounting perforation in base	no
Cover width	0 mm
Cover width 2	0 mm
Cover width 3	0 mm
Protection rating	IP40
Protective film	no
Protection rating IK code	IK08
Symmetrical	yes
Permitted temperature range, max.	60 °C
Permitted temperature range, min.	-15 °C
Angle range, max.	110 mm
Angle range, min.	80 mm