

Technical data sheet

End piece, for device installation trunking Rapid 45-2 type
GK-53100
Item number: 6113113



End piece for side closing of the Rapid 45-2 GK and GA 53100 device installation trunking.



PC/ABS Polycarbonate/Acrylonitrile-butadiene-styrene

Master data		
Item number	6113113	
Type	GK-E53100SW	
Description 1	End piece	
Description 2	for Rapid 45-2 100	
Manufacturer	OBO	
Dimension	106x56x22	
Colour	Jet black; RAL 9005	
Material	Polycarbonate/Acrylonitrile-butadiene-styrene	
Smallest sales unit	1	
Unit of quantity	Piece	
Weight	2.493 kg	
Weight unit	kg/100 pc.	
CO2 Footprint (GWP) Cradle-to-Gate	0,1966 kg CO2e / 1 Piece	

Dimensions		
Length	22 mm	
Width	106 mm	
Height	56 mm	

Technical data sheet

End piece, for device installation trunking Rapid 45-2 type
GK-53100

Item number: 6113113



Technical data

Version for	Symmetrical
Fastening type	Lockable
for duct width	100 mm
for trunking height	53 mm
Suitable for	Left/right
Halogen-free	yes
Cut lamination	yes
Protective film	no
Permitted temperature range, max.	60 °C
Permitted temperature range, min.	-5 °C