

Technical data sheet

Flat angle cover, for device installation trunking Rapid 80
type 70130

Item number: 6274423



Flat angle cover fitting made of halogen-free PC/ABS for simple creation of a rising or falling 90° change of direction with device installation trunking of the series Rapid 80 GK, GKH, GS and GA. The flat angle cover fitting can be used for symmetrical and asymmetrical trunking types.



Polycarbonate/Acrylnitrile-butadiene-styrene

Master data

| | |
|------------------------------------|--|
| Item number | 6274423 |
| Type | GK-FH70130SW |
| Description 1 | Flat angle |
| Description 2 | hood fitting |
| Manufacturer | OBO |
| Dimension | 70x130 |
| Colour | Jet black; RAL 9005 |
| Material | Polycarbonate/Acrylnitrile-butadiene-styrene |
| Smallest sales unit | 1 |
| Unit of quantity | Piece |
| Weight | 12.461 kg |
| Weight unit | kg/100 pc. |
| CO2 Footprint (GWP) Cradle-to-Gate | 1,2305 kg CO2e / 1 Piece |

Dimensions

| | |
|--------|----------|
| Length | 172.5 mm |
| Width | 138 mm |
| Height | 73 mm |

Technical data sheet

Flat angle cover, for device installation trunking Rapid 80
type 70130

Item number: 6274423



Technical data

| | |
|--------------------------------------|--------------------------|
| Number of covers | 1 |
| Version for | Hood fitting |
| for duct width | 130 mm |
| for trunking height | 70 mm |
| Halogen-free | yes |
| Cable retaining clip | no |
| Duct connector | no |
| Cover mounting type | Cross-over |
| Mounting perforation in base | no |
| Cover width | 0 mm |
| Cover width 2 | 0 mm |
| Cover width 3 | 0 mm |
| Change of direction | Vertical, rising/falling |
| Protective film | yes |
| Symmetrical | yes |
| Permitted temperature range, max. | 60 °C |
| Permitted temperature range, min. | -5 °C |
| Angle range, max. | 90 mm |
| Angle range, min. | 90 mm |