


Technical data sheet

Joint cover

Item number: 6113030



Joint cover for the cover of the Rapid 45-2 device installation trunking to hide cut edges and provide a tidy connection to installed Modul 45® devices.



Polycarbonate/Acrylnitrile-butadiene-styrene

Master data		
Item number	6113030	
Description 1	Joint cover	
Description 2	for Rapid 45-2 cover	
Manufacturer	OBO	
Dimension	48x20x20	
Colour	Pure white; RAL 9010	
Material	Polycarbonate/Acrylnitrile-butadiene-styrene	
Smallest sales unit	6	
Unit of quantity	Piece	
Weight	0.624 kg	
Weight unit	kg/100 pc.	
CO Footprint (GWP) Cradle-to-Gate	0,0896 kg COe / 1 Piece	


Technical data sheet

Joint cover

Item number: 6113030



Dimensions



Length	20 mm
Width	48 mm
Height	20 mm

Technical data

Version for	Cover cut lamination
Fastening type	Lockable
Shape	Symmetrical
for trunking height	53 mm
Halogen-free	yes
Cover width	45 mm
Protection rating	IP40
Protection rating IK code	IK08
Permitted temperature range, max.	60 °C
Permitted temperature range, min.	-15 °C