

Technical data sheet

End piece, for cable trunking type LKM 60150

Item number: 6249825



End piece for closing the LKM ducts.



St	Steel
FSK	Strip galvanized / plastic coated

Master data

Item number	6249825
Type	LKM E60150RW
Description 1	End piece
Manufacturer	OBO
Dimension	60x150mm
Colour	Pure white; RAL 9010
Material	Steel
Surface	Strip galvanized / plastic coated
Surface standard	DIN EN 10346
Smallest sales unit	10
Unit of quantity	Piece
Weight	9 kg
Weight unit	kg/100 pc.
CO2 Footprint (GWP) Cradle-to-Gate	0,3891 kg CO2e / 1 Piece


Technical data sheet

End piece, for cable trunking type LKM 60150

Item number: 6249825



Dimensions



Length	21 mm
Width	150 mm
Height	64 mm
Dimension a	150 mm
Dimension b	64 mm

Technical data

Version for	Left/right
Fastening type	Lockable
Maintain electrical functions	no
Halogen-free	yes
Protection rating	IP30
Protective film	no
Protection rating IK code	IK10
Permitted temperature range, max.	90 °C
Permitted temperature range, min.	-5 °C