


Technical data sheet

Duct clamp, LKM, for the maintenance of electrical function
E30–E90, for LKM cable duct LKM 80080
Item number: 6249881



Duct clamp for the metal cable routing duct type LKM 60100, prevents the cables falling out during installation. The duct clamp is essential if the duct is used in cable systems with integrated maintenance of electrical function to DIN 4102, Part 12. Easy mounting through insertion into the loop perforation and interconnection in the side wall.



- St** Steel
- FS** Strip galvanized

Master data


Item number	6249881
Type	LKM KF60100
Description 1	Trunking clamp
Description 2	function maintenance
Manufacturer	OBO
Dimension	98x48x29mm
Colour	zinc
Material	Steel
Surface	Strip galvanized
Surface standard	DIN EN 10346
Smallest sales unit	10
Unit of quantity	Piece
Weight	9.8 kg
Weight unit	kg/100 pc.
CO2 Footprint (GWP) Cradle-to-Gate	0,3317 kg CO2e / 1 Piece

Technical data sheet

Duct clamp, LKM, for the maintenance of electrical function
E30–E90, for LKM cable duct LKM 80080
Item number: 6249881



Dimensions



Length	29 mm
Width	98 mm
Height	48 mm

Technical data

Fastening type	Lockable
Maintain electrical functions for duct dimension	yes 60 x 100
Halogen-free	yes
With equipotential bonding	no
Cover width	100 mm
Protection rating	IP30
Protection rating IK code	IK10
Self-extinguishing	no
Permitted temperature range, max.	90 °C
Permitted temperature range, min.	-5 °C