

# Technical data sheet

## T piece, for cable trunking type LKM 60150

Item number: 6249728



T piece including cover for changing the direction of the LKM ducts.  
Equipotential bonding without additional aids, between base and cover



|            |                                   |
|------------|-----------------------------------|
| <b>St</b>  | Steel                             |
| <b>FSK</b> | Strip galvanized / plastic coated |

### Master data

|                                    |                                   |
|------------------------------------|-----------------------------------|
| Item number                        | 6249728                           |
| Type                               | LKM T60150RW                      |
| Description 1                      | T piece                           |
| Description 2                      | with cover                        |
| Manufacturer                       | OBO                               |
| Dimension                          | 60x150mm                          |
| Colour                             | Pure white; RAL 9010              |
| Material                           | Steel                             |
| Surface                            | Strip galvanized / plastic coated |
| Surface standard                   | DIN EN 10346                      |
| Smallest sales unit                | 1                                 |
| Unit of quantity                   | Piece                             |
| Weight                             | 87.6 kg                           |
| Weight unit                        | kg/100 pc.                        |
| CO2 Footprint (GWP) Cradle-to-Gate | 3,0294 kg CO2e / 1 Piece          |

# Technical data sheet


T piece, for cable trunking type LKM 60150

Item number: 6249728



## Dimensions

|             |        |
|-------------|--------|
| Length      | 300 mm |
| Width       | 150 mm |
| Height      | 64 mm  |
| Dimension a | 300 mm |



## Technical data

|                                   |                  |
|-----------------------------------|------------------|
| Departing width                   | 150 mm           |
| Departing height                  | 64 mm            |
| Version for                       | Base and cover   |
| Fastening type                    | Base perforation |
| Maintain electrical functions     | no               |
| for duct dimension                | 60 x 150         |
| Halogen-free                      | yes              |
| Duct height, min.                 | 64 mm            |
| Trunking depth                    | 64 mm            |
| Protection rating                 | IP30             |
| Protective film                   | no               |
| Protection rating IK code         | IK10             |
| Permitted temperature range, max. | 90 °C            |
| Permitted temperature range, min. | -5 °C            |