

Technical data sheet

Wiring trunking, type LKVH 50075

Item number: 6178588



Halogen-free wiring duct according to DIN EN 50085-2-3, incl. cover and base perforation, for horizontal and vertical routing of electrical cables in the switchgear cabinet. Designed as a DIN duct. Retainers are broken out without tools. The flush-floor routing of cables is possible through predetermined break points. Tested to DIN EN 50085-2-3. Special lengths on request.



PC/ABS Polycarbonate/Acrylnitrile-butadiene-styrene

Master data

Item number	6178588
Type	LKVH 50075
Description 1	Slotted cable trunking system
Description 2	halogen-free
Manufacturer	OBO
Dimension	50x75x2000
Colour	Light grey; RAL 7035
Material	Polycarbonate/Acrylnitrile-butadiene-styrene
Smallest sales unit	24
Unit of quantity	Metre
Weight	52 kg
Weight unit	kg/100 m


Technical data sheet

Wiring trunking, type LKVH 50075

Item number: 6178588



Dimensions



Length	2,000 mm
Width	75 mm
Height	50 mm

Technical data

Side wall version	Slotted
Fastening type	Base perforation
Flexible	no
Halogen-free	yes
Creepage current-resistant	yes
With cover	yes
Usable cross-section	31.6 cm ²
Slot spacing	12.5 mm
Slot width	5 mm
Self-extinguishing	yes
Permitted temperature range, max.	90 °C
Permitted temperature range, min.	-25 °C