

Technical data sheet

MS4141 mounting rail, slot 22 mm, FS, side perforation

Item number: 1123010



Heavy-duty C profile rail for individual installation of support constructions, e.g. for cable trays or as a panel for switchgear cabinets. Can also be used for cable routing, in conjunction with clamp clips with a U foot.



St	Steel
FS	Strip galvanized

Master data

Item number	1123010
Type	MSL4141PP3000FS
Description 1	Profile rail
Description 2	perforated, slot 22mm
Manufacturer	OBO
Dimension	3000x41x41
Material	Steel
Surface	Strip galvanized
Surface standard	DIN EN 10346
Smallest sales unit	3
Unit of quantity	Metre
Weight	179.4 kg
Weight unit	kg/100 m
CO Footprint (GWP) Cradle-to-Gate	4,7726 kg COe / 1 Meter


Technical data sheet

MS4141 mounting rail, slot 22 mm, FS, side perforation

Item number: 1123010



Dimensions



Length	3,000 mm
Width	41 mm
Height	41 mm
Dimension L	3,000 mm

Technical data

Breakable	no
Type of perforation	3 sides perforated
Version for	Single profile
Drill hole spacing, centre	50 mm
Maintain electrical functions	yes
Hole size	14x28 mm
Material thickness	2 mm
With perforation	no
With tothing	yes
Profile shape	C profile
Slot width	22 mm
Static value A	2.45 cm ²
Static value Iy	5.18 cm
Static value Iz	7.56 cm
Static value Wy	2.51 cm ²
Static value Wz	2.69 cm ²