

Technical data sheet

Installation socket, double, NF

Item number: 7408834



Installation socket for GES R2 floor socket for mounting in UD GES R2 screed box and in raised floor plates with an installation opening diameter of 122 mm.

The scope of delivery contains a double socket (NF). Up to two modular data sockets (Keystones) can be installed with optional mounting plate.



PA Polyamide

Master data

| | |
|---------------------|-----------------------------|
| Item number | 7408834 |
| Description 1 | Mounting support for GES R2 |
| Description 2 | with two times NF |
| Manufacturer | OBO |
| Colour | Graphite black; RAL 9011 |
| Material | Polyamide |
| Smallest sales unit | 1 |
| Unit of quantity | Piece |
| Weight | 21 kg |
| Weight unit | kg/100 pc. |

Dimensions

Technical data sheet

Installation socket, double, NF

Item number: 7408834



Technical data

| | |
|---|----------|
| Number of installable devices | 2 |
| Number of strain reliefs | 1 |
| Floor covering protection frame | no |
| Cover version | Round |
| Seal installation option | yes |
| Suitable for raised floor installation | yes |
| Suitable for cavity floor installation | yes |
| Suitable for wet care | no |
| Suitable for underfloor ducts | no |
| Device type | Grid M45 |
| Device support to accept mounting boxes | no |
| Installation technology | Grid M45 |
| With floor covering recess | no |
| Clamping range D, max. | 50 mm |
| Clamping range D, min. | 25 mm |
| Strain relief option | yes |