

Technical data sheet

Nail anchor N-K with nail head, A5

Item number: 3498392



The nail anchor N can be used for multiple fastenings of non-load-bearing systems in areas with highly corrosive impacts in cracked and non-cracked concrete, thereby combining the benefits of a bolt tie with even easier mounting.

The nail anchor only needs to be hammered into the drill hole. When the load occurs, the nail anchor spreads itself and bolts itself in the drill hole.

European technical approval ETA-11/0240, including characteristic values under fire exposure to fire resistance R 120.



A5 Stainless steel

Master data

Item number	3498392
Type	N-K 6-5/44 HCR
Description 1	Nail anchor N-K
Description 2	with nailhead
Manufacturer	OBO
Dimension	6x44mm
Colour	stainless steel
Material	Stainless steel
Smallest sales unit	50
Unit of quantity	Piece
Weight	1.135 kg
Weight unit	kg/100 pc.


Technical data sheet

Nail anchor N-K with nail head, A5

Item number: 3498392



Dimensions



Length	44 mm
Dimension d min.	13 mm
Dimension L	44 mm

Technical data

Version for	Lightning strike
Fastening unit	Miscellaneous
Drill hole depth	40 mm
Drill hole diameter, min.	6 mm
Clamping strength	5 mm
Self-drilling	no
Approvals available	yes
Suitable for material	Concrete
Mounting type, anchor, tie	Push-through mounting