

# Technical data sheet

## 90° Magic bend 60 A4

Item number: 6041206



90° bend with quick connector system. For all cable tray types of 60 mm side height.



**A4** Stainless steel

**2B** Bright, treated

### Master data

|                     |                      |
|---------------------|----------------------|
| Item number         | 6041206              |
| Description 1       | 90° bend             |
| Description 2       | with quick connector |
| Manufacturer        | OBO                  |
| Dimension           | 60x300               |
| Material            | Stainless steel      |
| Surface             | Bright, treated      |
| Surface standard    |                      |
| Smallest sales unit | 1                    |
| Unit of quantity    | Piece                |
| Weight              | 192.2 kg             |
| Weight unit         | kg/100 pc.           |

# Technical data sheet

## 90° Magic bend 60 A4

Item number: 6041206



### Dimensions



|                 |         |
|-----------------|---------|
| Width           | 300 mm  |
| Height          | 60 mm   |
| Plate thickness | 1.25 mm |
| Dimension B     | 300 mm  |

### Technical data

|                                         |                      |
|-----------------------------------------|----------------------|
| Bend (angle)                            | 90°                  |
| Connector version                       | Integrated connector |
| Maintain electrical functions           | yes                  |
| Mounting perforation in base            | no                   |
| NATO hole pattern                       | no                   |
| Change of direction                     | Horizontal           |
| Rustproof steel, pickled                | no                   |
| Side perforation                        | no                   |
| Wide-span version                       | no                   |
| Type of connector, cable support system | Click fastening      |