


Technical data sheet

Magic cross-over 85 FT

Item number: 7027107



Cross-over with quick connector system. For all cable tray types of 85 mm side height.



- St** Steel
- FT** Hot-dip galvanised

Master data

| | |
|---------------------|----------------------|
| Item number | 7027107 |
| Type | RKM 830 FT |
| Description 1 | Cross over |
| Description 2 | with quick connector |
| Manufacturer | OBO |
| Dimension | 85x300 |
| Material | Steel |
| Surface | Hot-dip galvanised |
| Surface standard | DIN EN ISO 1461 |
| Smallest sales unit | 1 |
| Unit of quantity | Piece |
| Weight | 280.5 kg |
| Weight unit | kg/100 pc. |


Technical data sheet

Magic cross-over 85 FT

Item number: 7027107



Dimensions



| | |
|-----------------|---------|
| Width | 300 mm |
| Height | 85 mm |
| Plate thickness | 1.25 mm |
| Dimension B | 300 mm |

Technical data

| | |
|---|----------------------|
| Bend (angle) | 90° |
| Connector version | Integrated connector |
| Maintain electrical functions | no |
| Material thickness, floor plate | 1.25 mm |
| NATO hole pattern | no |
| Change of direction | Horizontal |
| Rustproof steel, pickled | no |
| Wide-span version | no |
| Type of connector, cable support system | Click fastening |
| Rail thickness | 1.25 mm |