

# Technical data sheet

Height-adjustable heavy-duty cassette, blank, RKRSL, nominal size R9, stainless steel  
Item number: 7409114



Round, "blank", heavy-duty cassette of nominal size R9 for the creation of an inspection opening in trunking systems, raised and cavity floors, in dry or wet-cleaned floors for indoor use. Load class 2 to 20 kN. Only suitable for smooth floor coverings.

Height-adjustable heavy-duty cassette as a blind cassette with a load bearing capacity of 2–20 kN, 3-compartment. 3 APMT5 cover plates can be installed. For the installation of 3 UT4 universal supports for 9 individual installation devices with support ring/support clamp or 12 Modul 45 devices.  
Height-adjustable round heavy-duty cassette as blanking cassette to create an inspection opening. For the installation in trunking systems, raised and cavity floors in dry- or wet-cleaned floors in indoor areas. Load class 2 to 20 kN.



A2 Stainless steel

## Master data


Item number	7409114
Type	RKR2 9SL2 V2 25
Description 1	Heavy-duty cassette
Description 2	blank, 20 kN
Manufacturer	OBO
Dimension	Ø305mm
Material	Stainless steel 1.4301
Smallest sales unit	1
Unit of quantity	Piece
Weight	620 kg
Weight unit	kg/100 pc.
CO2 Footprint (GWP) Cradle-to-Gate	23,8324 kg CO2e / 1 Piece

# Technical data sheet

Height-adjustable heavy-duty cassette, blank, RKRSL, nominal size R9, stainless steel  
Item number: 7409114



## Dimensions



Dimension h 109 mm

## Technical data

Number of installable devices	0
Version for	Round
Cable outlet version	No cable outlet
Floor care	Wet
Decouplable	no
Floor height, max.	159 mm
Floor height, min.	109 mm
Suitable for raised floor installation	yes
Suitable for cavity floor installation	yes
Suitable for underfloor box	350
Device support to accept mounting boxes	yes
Nominal size for device installation units	R9
Height-adjustment range, max.	159 mm
Height-adjustment range, min.	109 mm
Protection rating (IP) when used	IP00
Protection rating (IP) when unused	IP44
Protection rating IK code	IK10
Heavy-duty version	yes
Heavy load class	20 kN (OBO SL2)
Installation system type	UT4
Floor covering thickness	25 mm