


Technical data sheet

T branch piece FT

Item number: 7119550



Horizontal T branch piece, for all cable tray types of 110 mm side height.
Fitting in round design. The interior radius of the fitting is 150 mm. All the sides are designed for the same cable tray width.
Fastening materials should be ordered separately.




St Steel

FT Hot-dip galvanised

Master data

Item number	7119550
Type	RT 155 FT
Description 1	T-branch piece
Description 2	horizontal, round type
Manufacturer	OBO
Dimension	110x550
Material	Steel
Surface	Hot-dip galvanised
Surface standard	DIN EN ISO 1461
Smallest sales unit	1
Unit of quantity	Piece
Weight	1100 kg
Weight unit	kg/100 pc.

Dimensions



Width	550 mm
Width	22 in
Height	110 mm
Dimension B	550 mm
Dimension R	150 mm

Technical data sheet

T branch piece FT

Item number: 7119550



Technical data

Bend (angle)	90°
Connector version	Without connectors
Maintain electrical functions	no
NATO hole pattern	no
Change of direction	Horizontal
Rustproof steel, pickled	no
Wide-span version	no
Type of connector, cable support system	Screwed
Rail thickness	1.25 mm