


Technical data sheet

Underfloor installation duct, 2-compartment, trunking
height 48 mm
Item number: 7400308



Underfloor installation duct for laying cables under the floor.



- St Steel
- FS Strip galvanized

Master data	
Item number	7400308
Type	S2 19048
Description 1	Underfloor duct
Description 2	2 compartments
Manufacturer	OBO
Dimension	2000x190x48
Material	Steel
Surface	Strip galvanized
Surface standard	DIN EN 10346
Smallest sales unit	2
Unit of quantity	Metre
Weight	376 kg
Weight unit	kg/100 m
CO Footprint (GWP) Cradle-to-Gate	8,6764 kg COe / 1 Meter


Technical data sheet

Underfloor installation duct, 2-compartment, trunking
height 48 mm

Item number: 7400308



Dimensions



Length	2,000 mm
Width	190 mm
Height	48 mm
Dimension a	80 mm
Dimension b	110 mm
Dimension h	48 mm

Technical data

Number of fixed partitions	1
Number of compartments	2 St.
Mounting system fastening type	Floor
Floor plate	yes
Application area	Screed-covered
Decouplable	no
Duct height, min.	48 mm
Usable cross-section	8556 mm ²
Removable cover	no
Cross-section, draw a	3588 mm ²
Cross-section, draw b	4968 mm ²