


Technical data sheet

Electrogalvanised steel pipe, without thread

Item number: 2046844



Electrical installation pipe without threaded ends according to EN 61386-1 for mechanical protection of cables. With burr-free inner wall.



St	Steel
G	Electrogalvanized

Master data

Item number	2046844
Type	S40W G
Description 1	Plug-in conduit
Description 2	without thread
Manufacturer	OBO
Dimension	Ø40, 3000mm
Material	Steel
Surface	Electrogalvanized
Surface standard	EN ISO 19598 / EN ISO 4042
Smallest sales unit	15
Unit of quantity	Metre
Weight	139.7 kg
Weight unit	kg/100 m
CO Footprint (GWP) Cradle-to-Gate	2,6699 kg COe / 1 Meter


Technical data sheet

Electrogalvanised steel pipe, without thread

Item number: 2046844



Dimensions



Length	3,000 mm
Dimension D	40 mm
Dimension L	3,000 mm
Dimension m (mm)	M40
Dimension t	1.2 mm



Technical data sheet

Electrogalvanised steel pipe, without thread

Item number: 2046844



Technical data

Surface-mounted	yes
Pipe version	Rigid without thread
Concrete installation	yes
Bending behaviour	rigid
Pressure resistance	Heavy (1,250 N)
Use temperature, max.	+ 400 °C
Use temperature, min.	- 45 °C
Cavity wall installation	yes
Installation on wood	yes
Installation in the earth	no
Installation outdoors	no
Classification code	44571
Machines and system installation	no
With sleeve	no
Brushed surface	no
Polished surface	no
Impact resistance	Heavy (2.0 kg/300 mm)
Permitted temperature range, max.	400 °C
Permitted temperature range, min.	-45 °C
Underfloor installation (bitumen, hot asphalt)	yes
Underfloor installation (screed)	yes
Concealed	yes