# **Technical data sheet**

33° socket, protective contact, double

### Item number: 6120114



Protective contact socket, double 33°, with increased touch protection, with screwless terminals, 2-pin, 16 A, 250 V~, with connection terminals to IEC 60884-1.

For installation in Rapid 45 ducts, device installation ducts, installation columns, underfloor systems and Deskboxes.





PC Polycarbo

#### Master data

Item number	6120114	
Description 1	Socket 33°, double	
Description 2	protective contact	
Manufacturer	OBO	
Dimension	250V, 10/16A	
Colour	Aluminium painted	
Material	Polycarbonate	
Smallest sales unit	1	
Unit of quantity	Piece	
Weight	7.7 kg	
Weight unit	kg/100 pc.	
CO Footprint (GWP) Cradle-to- Gate	0,3349 kg COe / 1 Piece	

## **Technical data sheet**

33° socket, protective contact, double

### Item number: 6120114



Dimensions		
	Width	90 mm
Londer 7	Height	45 mm

Т	ec	hni	ical	da	ita

Cover	Central plate
Closable	no
Connection type	Screwless terminal
Number of units	2
Number of modules (for modular construction)	ō
Number of switchable sockets	0
Number of poles	2
Printed label/coding	Without printing
Version for	double 33°
Surface version	Matt
Version for	SCHUKO
Ejection mechanism	no
Fastening type	Lock
Labelling panel	no
Operating temperature, max.	40 °C
Operating temperature, min.	-5 °C
increased touch protection	ves
Error current protection	no
For more difficult conditions (ac- cording to VDE)	no
Halogen-free	yes
Insulated installation	no
Hinged cover	no
Coding	no
Warning light	no
With on/off switch	no
With fine-wire fuse	no
With functional lighting	no
With orientation lighting	no
Mounting type	Device installation duct
Nominal voltage	250 V
Nominal current	16 A
Protection rating	Other
Special power supply	Without special power supply
Socket version	Protective contact
Socket angle	33°
Depth	42 mm
Transparent	no
Rotated central insert	yes
Approvals	VDE