

Technical data sheet

33° socket, Connect 45, with earthing pin, triple, black-grey

Item number: 6120700



Socket with earthing pin and side connection, Triple 33°, with increased touch protection, with screwless terminals, 2-pin, 16 A, 250 V~, with connection terminals to IEC 60884-1.

For installation in Rapid 45 trunking, device installation trunking, service poles, underfloor systems and desk boxes.



PC Polycarbonate

Master data

| | |
|------------------------------------|----------------------------|
| Item number | 6120700 |
| Type | STD-F3C SWGR3 |
| Description 1 | Socket 33°, triple |
| Description 2 | with earth pin, Connect 45 |
| Manufacturer | OBO |
| Dimension | 250V, 10/16A |
| Colour | Black-grey; RAL 7021 |
| Material | Polycarbonate |
| Smallest sales unit | 1 |
| Unit of quantity | Piece |
| Weight | 11.5 kg |
| Weight unit | kg/100 pc. |
| CO2 Footprint (GWP) Cradle-to-Gate | 0,2115 kg CO2e / 1 Piece |


Technical data sheet

33° socket, Connect 45, with earthing pin, triple, black-grey


Item number: 6120700



Dimensions



| | |
|--------|--------|
| Width | 135 mm |
| Height | 45 mm |



Technical data

| | |
|--|------------------------------|
| Cover | Central plate |
| Closable | no |
| Connection type | Screwless terminal |
| Number of units | 3 |
| Number of modules (for modular construction) | 3 |
| Number of switchable sockets | 0 |
| Number of poles | 2 |
| Printed label/coding | Without printing |
| Version for | Triple 33° |
| Surface version | Matt |
| Version for | Protective contact pin |
| Ejection mechanism | no |
| Fastening type | Lock |
| Labelling panel | no |
| Operating temperature, max. | 40 °C |
| Operating temperature, min. | -5 °C |
| increased touch protection | yes |
| Error current protection | no |
| For more difficult conditions (according to VDE) | no |
| Halogen-free | yes |
| Insulated installation | no |
| Hinged cover | no |
| Coding | no |
| Warning light | no |
| With on/off switch | no |
| With fine-wire fuse | no |
| With functional lighting | no |
| With orientation lighting | no |
| Mounting type | Device installation duct |
| Nominal voltage | 250 V |
| Nominal current | 16 A |
| Protection rating | Other |
| Special power supply | Without special power supply |
| Socket version | NF |

Technical data sheet

33° socket, Connect 45, with earthing pin, triple, black-grey

Item number: 6120700



Technical data

| | |
|------------------------|-------|
| Socket angle | 33° |
| Depth | 37 mm |
| Transparent | no |
| Rotated central insert | yes |
| Approvals | VDE |
| Surge protection | no |