

Technical data sheet

Flat angle cover, trunking type WDKH 30045

Item number: 6176040



Flat angle hood for changing the direction of the halogen-free WDKH trunking.



Polycarbonate/Acrylnitrile-butadiene-styrene

Master data

Item number	6176040
Type	WDKH-F30045LGR
Description 1	Flat angle cover
Description 2	halogen-free
Manufacturer	OBO
Dimension	30x45mm
Colour	Light grey; RAL 7035
Material	Polycarbonate/Acrylnitrile-butadiene-styrene
Smallest sales unit	4
Unit of quantity	Piece
Weight	1.652 kg
Weight unit	kg/100 pc.
CO2 Footprint (GWP) Cradle-to-Gate	0,1132 kg CO2e / 1 Piece

Technical data sheet

Flat angle cover, trunking type WDKH 30045

Item number: 6176040



Dimensions



Length	68 mm
Width	45 mm
Height	30 mm
Dimension a	60 mm

Technical data

Version for	Hood fitting
Fastening type	Lockable
Maintain electrical functions for duct dimension	no 30 x 45
Halogen-free	yes
Duct height, min.	45 mm
Trunking depth	30 mm
Protection rating	IP30
Protective film	no
Protection rating IK code	IK07.
Self-extinguishing	yes
Permitted temperature range, max.	90 °C
Permitted temperature range, min.	-5 °C
Angle range, max.	90 mm
Angle range, min.	90 mm