

Technical data sheet

Mini trunking with adhesive film and hinged cover MD7

Item number: 6150276



Mini trunking with adhesive film and hinge cover.
Pulling off the film on the base allows the WDK trunking to be stuck directly on the wall.



PVC Polyvinylchloride

Master data

Item number	6150276
Type	WDKMD7RW
Description 1	Mini trunking w. adhesive film
Description 2	and hinged upper part
Manufacturer	OBO
Dimension	7x12,5x2000
Colour	Pure white; RAL 9010
Material	Polyvinylchloride
Smallest sales unit	2
Unit of quantity	Metre
Weight	5 kg
Weight unit	kg/100 m
CO Footprint (GWP) Cradle-to-Gate	0,0929 kg COe / 1 Meter


Technical data sheet

Mini trunking with adhesive film and hinged cover MD7

Item number: 6150276



Dimensions



Length	2,000 mm
Width	12.5 mm
Height	7 mm

Technical data

Number of fixed partitions	0
Number of insertable partitions	0
Version, cable trunking cover	With film hinge
Fastening type	Self-adhesive
Base perforation	0
Maintain electrical functions	no
Halogen-free	no
Cable retaining clip	no
Duct connector	no
Delivery on a roll	no
Usable cross-section	49 mm ²
Protective film	no