

Technical data sheet

End piece, trunking type WDK 100230

Item number: 6163076



End piece to close the WDK trunking.
The end pieces are pushed onto the WDK trunking and are fixed on the floor connector by spring force.



PVC Polyvinylchloride

Master data

Item number	6163076
Type	WDK HE100230CW
Description 1	End piece
Manufacturer	OBO
Dimension	100x230mm
Colour	Cream; RAL 9001
Material	Polyvinylchloride
Smallest sales unit	5
Unit of quantity	Piece
Weight	10.237 kg
Weight unit	kg/100 pc.
CO2 Footprint (GWP) Cradle-to-Gate	0,2615 kg CO2e / 1 Piece

Technical data sheet

End piece, trunking type WDK 100230

Item number: 6163076



Dimensions



Length	25 mm
Width	230 mm
Height	100 mm
Dimension a	230 mm
Dimension b	100 mm
Dimension H	230 mm

Technical data

Version for	Left/right
Fastening type	Lockable
Maintain electrical functions	no
Halogen-free	no
Protection rating	IP30
Protective film	no
Protection rating IK code	IK04
Permitted temperature range, max.	60 °C
Permitted temperature range, min.	-5 °C