

Technical data sheet

End piece, trunking type WDK 30045

Item number: 6183700



End piece to close the WDK trunking.
The end pieces are pushed onto the WDK trunking and are fixed on the floor connector by spring force.



PVC Polyvinylchloride

Master data

Item number	6183700
Type	WDK HE30045LGR
Description 1	End piece
Manufacturer	OBO
Dimension	30x45mm
Colour	Light grey; RAL 7035
Material	Polyvinylchloride
Smallest sales unit	10
Unit of quantity	Piece
Weight	0.509 kg
Weight unit	kg/100 pc.
CO2 Footprint (GWP) Cradle-to-Gate	0,0313 kg CO2e / 1 Piece

Technical data sheet

End piece, trunking type WDK 30045

Item number: 6183700



Dimensions



Length	17 mm
Width	45 mm
Height	30 mm
Dimension a	45 mm
Dimension b	30 mm
Dimension H	45 mm

Technical data

Version for	Left/right
Fastening type	Lockable
Maintain electrical functions	no
Halogen-free	no
Protection rating	IP30
Protective film	no
Protection rating IK code	IK04
Permitted temperature range, max.	60 °C
Permitted temperature range, min.	-5 °C