

Technical data sheet

Flat angle cover, for trunking type WDK 15040

Item number: 6161227



Flat angle hood for changing the direction of the WDK trunking.



PVC Polyvinylchloride

Master data

Item number	6161227
Type	WDK HF15040CW
Description 1	Flat angle cover
Manufacturer	OBO
Dimension	15x40mm
Colour	Cream; RAL 9001
Material	Polyvinylchloride
Smallest sales unit	4
Unit of quantity	Piece
Weight	1.5 kg
Weight unit	kg/100 pc.
CO2 Footprint (GWP) Cradle-to-Gate	0,0431 kg CO2e / 1 Piece

Technical data sheet

Flat angle cover, for trunking type WDK 15040

Item number: 6161227



Dimensions



Length	63 mm
Width	40 mm
Height	15 mm
Dimension a	63 mm
Dimension H	40 mm

Technical data

Version for	Hood fitting
Fastening type	Lockable
Maintain electrical functions for duct dimension	no 15 x 40
Halogen-free	no
Trunking depth	15 mm
Protection rating	IP30
Protective film	no
Protection rating IK code	IK04
Permitted temperature range, max.	60 °C
Permitted temperature range, min.	-5 °C
Angle range, max.	90 mm
Angle range, min.	90 mm