

Technical data sheet

Flat angle cover, trunking type WDK 30030

Item number: 6183298



Flat angle hood for changing the direction of the WDK trunking.



PVC Polyvinylchloride

Master data

| | |
|------------------------------------|--------------------------|
| Item number | 6183298 |
| Type | WDK HF30030LGR |
| Description 1 | Flat angle cover |
| Manufacturer | OBO |
| Dimension | 30x30mm |
| Colour | Light grey; RAL 7035 |
| Material | Polyvinylchloride |
| Smallest sales unit | 4 |
| Unit of quantity | Piece |
| Weight | 1.37 kg |
| Weight unit | kg/100 pc. |
| CO2 Footprint (GWP) Cradle-to-Gate | 0,0397 kg CO2e / 1 Piece |

Technical data sheet

Flat angle cover, trunking type WDK 30030

Item number: 6183298



Dimensions



| | |
|-------------|-------|
| Length | 53 mm |
| Width | 30 mm |
| Height | 30 mm |
| Dimension a | 53 mm |
| Dimension H | 30 mm |

Technical data

| | |
|--|---------------|
| Version for | Hood fitting |
| Fastening type | Lockable |
| Maintain electrical functions for duct dimension | no 30 x 30 |
| Halogen-free | no |
| Trunking depth | 30 mm |
| Protection rating | IP30 |
| Protective film | no |
| Protection rating IK code | IK04 |
| Permitted temperature range, max. | 60 °C |
| Permitted temperature range, min. | -5 °C |
| Angle range, max. | 90 mm |
| Angle range, min. | 90 mm |