

# Technical data sheet

## Flat angle cover, trunking type WDK 40040

Item number: 6161294



Flat angle cover for changing the direction of the WDK trunking.



**PVC** Polyvinylchloride

### Master data

Item number	6161294
Type	WDK HF40040CW
Description 1	Flat angle cover
Manufacturer	OBO
Dimension	40x40mm
Colour	Cream; RAL 9001
Material	Polyvinylchloride
Smallest sales unit	4
Unit of quantity	Piece
Weight	2.534 kg
Weight unit	kg/100 pc.
CO2 Footprint (GWP) Cradle-to-Gate	0,0868 kg CO2e / 1 Piece

# Technical data sheet

Flat angle cover, trunking type WDK 40040

Item number: 6161294



## Dimensions



Length	63 mm
Width	40 mm
Height	40 mm
Dimension a	63 mm
Dimension H	40 mm

## Technical data

Version for	Hood fitting
Fastening type	Lockable
Maintain electrical functions for duct dimension	no 40 x 40
Halogen-free	no
Trunking depth	40 mm
Protection rating	IP30
Protective film	no
Protection rating IK code	IK04
Permitted temperature range, max.	60 °C
Permitted temperature range, min.	-5 °C
Angle range, max.	90 mm
Angle range, min.	90 mm