

# Technical data sheet

## Flat angle cover, trunking type WDK 60230

Item number: 6161596



Flat angle hood for changing the direction of the WDK trunking.



**PVC** Polyvinylchloride

### Master data

Item number	6161596
Type	WDK HF60230CW
Description 1	Flat angle cover
Manufacturer	OBO
Dimension	60x230mm
Colour	Cream; RAL 9001
Material	Polyvinylchloride
Smallest sales unit	2
Unit of quantity	Piece
Weight	47.856 kg
Weight unit	kg/100 pc.
CO2 Footprint (GWP) Cradle-to-Gate	1,0978 kg CO2e / 1 Piece

# Technical data sheet

Flat angle cover, trunking type WDK 60230

Item number: 6161596



## Dimensions



Length	270 mm
Width	230 mm
Height	60 mm
Dimension a	270 mm
Dimension H	230 mm

## Technical data

Version for	Hood fitting
Fastening type	Lockable
Maintain electrical functions for duct dimension	no 60 x 230
Halogen-free	no
Trunking depth	60 mm
Protection rating	IP30
Protective film	no
Protection rating IK code	IK04
Permitted temperature range, max.	60 °C
Permitted temperature range, min.	-5 °C
Angle range, max.	90 mm
Angle range, min.	90 mm