


Technical data sheet

T and intersection cover, for trunking type WDK 60170

Item number: 6192661



T and intersection cover for changing the direction of the WDK trunking. The fitting is preperforated at the side for the connection of different trunking cross-sections.



PVC Polyvinylchloride

Master data

Item number	6192661
Type	WDK HK60170RW
Description 1	T- and crosspiece cover
Manufacturer	OBO
Dimension	60x170mm
Colour	Pure white; RAL 9010
Material	Polyvinylchloride
Smallest sales unit	2
Unit of quantity	Piece
Weight	32.6 kg
Weight unit	kg/100 pc.
CO2 Footprint (GWP) Cradle-to-Gate	0,678 kg CO2e / 1 Piece

Technical data sheet

T and intersection cover, for trunking type WDK 60170

Item number: 6192661



Dimensions



Length	291 mm
Width	170 mm
Height	60 mm
Dimension a	291 mm
Dimension b	66 mm
Dimension H	170 mm

Technical data

Version for	Hood fitting
Fastening type	Lockable
Maintain electrical functions	no
for duct dimension	60 x 170
Protection rating	IP30
Protection rating IK code	IK04
Permitted temperature range, max.	60 °C
Permitted temperature range, min.	-5 °C