


Technical data sheet

Washer

Item number: 3402126



Washer according to DIN 125, shape A, for universal use.



St	Steel
G	Electrogalvanized

Master data

Item number	3402126
Type	WS M12 D24 G
Description 1	Washer
Manufacturer	OBO
Dimension	M12
Material	Steel
Surface	Electrogalvanized
Surface standard	EN ISO 19598 / EN ISO 4042
Smallest sales unit	100
Unit of quantity	Piece
Weight	0.57 kg
Weight unit	kg/100 pc.
CO Footprint (GWP) Cradle-to-Gate	0,0156 kg COe / 1 Piece

Dimensions




Plate thickness	0.1 in
Dimension D	0.94 in
Dimension d	0.51 in
Dimension d	13 mm
Dimension d min.	24 mm
Dimension h	2.5 mm

Technical data sheet

Washer

Item number: 3402126



Technical data

Faceted	no
Hardened	no
Thread	M12
Inner diameter	13 mm
Material thickness	2.5 mm
With tothing	no
Hole shape	Round