

Technical data sheet

Insulated air-termination rod for inner-routed isCon® conductor

Item number: 5408858



- For routing OBO isCon® conductors in pipes
- For installation on the building structure with isFang support
- Suitable for wind loads according to Eurocode 1: DIN EN 1991-1-4
- Tested according to VDE V 0185-561-8 (IEC TS 62561-8)
- Aluminium standpipe and air-termination tip
- Centre section made of fibre-glass reinforced plastic (GRP)



GFK Fibre-glass-reinforced plastic

Master data

Item number	5408858
Description 1	Insulated interception rod
Description 2	for isCon conductor, internal
Manufacturer	OBO
Dimension	8000mm
Material	Fibre-glass-reinforced plastic
Smallest sales unit	1
Unit of quantity	Piece
Weight	1315.741 kg
Weight unit	kg/100 pc.

Technical data sheet

Insulated air-termination rod for inner-routed isCon® conductor

Item number: 5408858



Dimensions	
	Length
	8,000 mm
	Dimension A
	5,335 mm
	Dimension B
	1,000 mm
	Dimension d min.
	50 mm
	Dimension H
	1,500 mm
	Dimension L
	8,000 mm

Technical data	
Connection	Round conductor
Version for	Air-termination rod
High voltage-resistant, insulated version	yes