

# Technical data sheet

## Cone cable gland, PG thread, small cutting ring, nickel-plated

Item number: 2082489



Cable gland with hexagonal intermediate connector, shape C4, to DIN 46320 with Pg connection thread to DIN 40430.

Pressure rings made of electrogalvanised and transparently passivated steel.

NR/SBR sealing ring.

Protection rating: with connection thread sealing ring IP 65, without connection thread sealing ring IP 54.

With simple sealing ring, with small internal diameter.

\* Prices according to DEL notation.



Brass



Nickel-plated

### Master data

Item number	2082489
Type	163 MS PG48
Description 1	Cable gland
Manufacturer	OBO
Dimension	PG48
Material	Brass
Surface	Nickel-plated
Surface standard	
Smallest sales unit	5
Unit of quantity	Piece
Weight	30.05 kg
Weight unit	kg/100 pc.


# Technical data sheet

Cone cable gland, PG thread, small cutting ring, nickel-plated

Item number: 2082489



## Dimensions



Dimension E	69 mm
Dimension L	44 mm
Dimension L max.	44 mm
Dimension L1	10 mm
Dimension L2	23 mm
Dimension L3	6 mm

## Technical data

Type of seal	Sealing ring
Bend protection	no
Sealing area D, max.	45 mm
Sealing area D, min.	43 mm
explosion-proof	no
Flat cable gland	no
For Ex zone	Without
Thread	Pg 48
Thread type	PG
Thread length	10 mm
Fibre-glass reinforced	no
Halogen-free	no
Sealing insert, multiple	no
With locknut	no
Impact-resistant	no
WAF 1	64 mm
WAF 2	60 mm
Protection rating	IP54
Strain relief option	no